



Tango MMF383

MMF383 HPI-TP250W 220V-50Hz A

MASTER HPI-T Plus, 250 W, Asymmetrical

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Cap-Base	E40 [E40]
Gear	HGR [HPL/HPI gear]
Light Technical	
Number of light sources	1
Optic type outdoor	Asymmetrical
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	250 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MMF383 HPI-TP250W 220V-50Hz A
Full product name	MMF383 HPI-TP250W 220V-50Hz A
Full product code	910401966580
Order code	910401966580
Material Nr. (12NC)	910401966580
Local order code	MMF383 250A
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Tango MMF383

Dimensional drawing

