



Pacific II TCW097

TCW097 1xTL-D18W I

1, MASTER TL-D, 18 W


Functional impact-, dust- and jetproof luminaire for single and twin TLD and TL5 fluorescent lamps for indoor applications and semioutdoor applications. Housing and cover of TCW097 are made of high quality poly-carbonate which has an excellent impact resistant property. The cover has anti-UV additives which bring additional performance levels to UV protection. Available with conventional or high-frequency (HF) electronic control gears. Can be ceiling mounted or suspended. Equipped with mounting brackets, mounting is made easy via screws without drilling into the luminaire housing. Gear tray and metal toggles are re-installed; cable gland and mounting brackets are delivered with the luminaire.

Product data

General Information		Protection class IEC	
Lamp family code	TL-D [MASTER TL-D]	Protection class IEC	Safety class I
Number of gear units	1 unit	Product Data	
Gear	CONV [Conventional]	Order product name	TCW097 1xTL-D18W I
Light Technical		Full product name	TCW097 1xTL-D18W I
Number of light sources	1	Full product code	910401983880
Operating and Electrical		Order code	910401983880
Input Voltage	220 V	Material Nr. (12NC)	910401983880
Line Frequency	50 Hz	Numerator - Quantity Per Pack	1
Power Consumption	18 W	Numerator - Packs per outer box	8
Approval and Application			
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]		

Pacific II TCW097

Dimensional drawing



TCW097	118	136	158	218	236	258
	114	128	135	214	228	235
LxWxH(mm)	660x100x110	1270x100x110	1570x100x110	660x150x110	1270x150x110	1570x150x110

