



Crestbay HPK888

HPK888 1xHPI-P250W-BU IC R-L WH

1, MASTER HPI Plus, 250 W, Reflector large, White

Reliable, effective lighting in any setting is a crucial factor that promotes the senses, productivity, safety and even architecture. Crestbay™ from Philips is precisely designed with this in mind. This highly versatile luminaire delivers outstanding performance in large spaces and in the toughest of environments while assuring quality lighting across a variety of industrial and commercial applications. Moreover, Crestbay™'s innovative SWING-2-BRIGHT™ technology makes maintenance easy, hassle-free and faster than ever before.”

Product data

General Information		Approval and Application	
Lamp family code	HPI-P [MASTER HPI Plus]	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Gear	CONV [Conventional]		
Light Technical		Product Data	
Number of light sources	1	Order product name	HPK888 1xHPI-P250W-BU IC R-L WH
Optic type	Reflector large	Full product name	HPK888 1xHPI-P250W-BU IC R-L WH
Optical cover type	-	Full product code	910402000180
		Order code	910402000180
		Material Nr. (12NC)	910402000180
Operating and Electrical		Numerator - Quantity Per Pack	1
Input Voltage	220 V	Numerator - Packs per outer box	1
Line Frequency	50 Hz		
Power Consumption	250 W		
Mechanical and Housing			
Housing Color	White		

Crestbay HPK888

Dimensional drawing

