



Lineco TMS022 UK

TMS022 2xTL-D70W/840 HFPUK

TMS022, 2, MASTER TL-D, 70 W, 840 neutral white, HF Performer

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Product data


General Information		Power Consumption	
Lamp family code	TL-D [MASTER TL-D]		70 W
Gear	HFP [HF Performer]	Mechanical and Housing	
Product family code	TMS022 [TMS022]	Fixation point length distance (Nom)	1,500 mm
CE mark	Yes	Overall length	1,787 mm
Flammability mark	For mounting on normally flammable surfaces	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP20 [Finger-protected]
Glow-wire test	Temperature 650 °C, duration 5 s	Mech. impact protection code	IK02 [0.2 J standard]
Light Technical		Protection class IEC	Safety class I
Number of light sources	2	Application Conditions	
Light source color	840 neutral white	Suitable for random switching	Not applicable
Optic type	-	Product Data	
Operating and Electrical		Order product name	TMS022 2xTL-D70W/840 HFPUK
Input Voltage	230 to 240 V	Full product name	TMS022 2xTL-D70W/840 HFPUK

Lineco TMS022 UK

Full product code	871155911634100
Order code	910402201484
Material Nr. (12NC)	910402201484
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559116341

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559116341

Dimensional drawing



Product

TMS022 2xTL-D70W/840 HFPUK

