



Lineco TMS022

TMS022 1xTL-D18W HFS

TMS022, 1, MASTER TL-D, 18 W, HF Standard

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Product family code	TMS022 [TMS022]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s

Light Technical

Number of light sources	1
Optic type	-

Operating and Electrical

Input Voltage	230 to 240 V
Power Consumption	18 W

Mechanical and Housing

Fixation point length distance (Nom)	900 mm
--------------------------------------	--------

Overall length	1,225 mm
----------------	----------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------


Product Data

Order product name	TMS022 1xTL-D18W HFS
Full product name	TMS022 1xTL-D18W HFS
Full product code	871155911870399
Order code	910402201603
Material Nr. (12NC)	910402201603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559118703
Numerator - Packs per outer box	12

Lineco TMS022

EAN/UPC - Case	8711559118710
----------------	---------------

Dimensional drawing



Product
TMS022 1xTL-D18W HFS

