



Lineco TMS022

TMS022 1xTL-D58W/840 HFRUK

TMS022, 1, MASTER TL-D, 58 W, 840 neutral white, HF Regulator

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Product data


General Information		Power Consumption	
Lamp family code	TL-D [MASTER TL-D]	58 W	
Gear	HFR [HF Regulator]	Mechanical and Housing	
Product family code	TMS022 [TMS022]	Fixation point length distance (Nom)	300 mm
CE mark	Yes	Overall length	462 mm
Flammability mark	For mounting on normally flammable surfaces	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP20 [Finger-protected]
Glow-wire test	Temperature 650 °C, duration 5 s	Mech. impact protection code	IK02 [0.2 J standard]
Light Technical		Protection class IEC	Safety class I
Number of light sources	1	Application Conditions	
Light source color	840 neutral white	Suitable for random switching	Not applicable
Optic type	-	Product Data	
Operating and Electrical		Order product name	TMS022 1xTL-D58W/840 HFRUK
Input Voltage	230 to 240 V	Full product name	TMS022 1xTL-D58W/840 HFRUK

Lineco TMS022

Full product code	871155911706500
Order code	910402204284
Material Nr. (12NC)	910402204284
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559117065

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559117065

Dimensional drawing



Product
TMS022 1xTL-D58W/840 HFRUK

