



# Lineco TMS022

## TMS022 1xTL-D36W HFS

TMS022, 1, MASTER TL-D, 36 W, HF Standard

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Product family code	TMS022 [TMS022]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s

### Light Technical

Number of light sources	1
Optic type	-

### Operating and Electrical

Input Voltage	230 to 240 V
Power Consumption	36 W

### Mechanical and Housing

Fixation point length distance (Nom)	1,500 mm
--------------------------------------	----------

Overall length	1,787 mm
----------------	----------

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------


### Product Data

Order product name	TMS022 1xTL-D36W HFS
Full product name	TMS022 1xTL-D36W HFS
Full product code	871155913556499
Order code	13556499
Material Nr. (12NC)	910402207403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559135564
Numerator - Packs per outer box	12

Lineco TMS022

EAN/UPC - Case	8711559135571
----------------	---------------

Dimensional drawing



Product
TMS022 1xTL-D36W HFS

