



Lineco TMS022 UK

TMS022 1xTL-D36W/840 HFSUK

TMS022, 1, MASTER TL-D, 36 W, 840 neutral white, HF Standard

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.


Product data

General Information		Mechanical and Housing	
Lamp family code	TL-D [MASTER TL-D]	Fixation point length distance (Nom)	900 mm
Gear	HFS [HF Standard]	Overall length	1,225 mm
Product family code	TMS022 [TMS022]	Approval and Application	
CE mark	Yes	Ingress protection code	IP20 [Finger-protected]
Flammability mark	For mounting on normally flammable surfaces	Mech. impact protection code	IK02 [0.2 J standard]
ENEC mark	ENEC mark	Protection class IEC	Safety class I
Glow-wire test	Temperature 650 °C, duration 5 s	Application Conditions	
Light Technical		Suitable for random switching	Not applicable
Number of light sources	1	Product Data	
Light source color	840 neutral white	Order product name	TMS022 1xTL-D36W/840 HFSUK
Optic type	-	Full product name	TMS022 1xTL-D36W/840 HFSUK
Operating and Electrical		Full product code	871155913565600
Input Voltage	230 to 240 V	Order code	910402207903
Power Consumption	36 W	Material Nr. (12NC)	910402207903
		Numerator - Quantity Per Pack	1

Lineco TMS022 UK

EAN/UPC - Product/Case	8711559135656
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559135656

Dimensional drawing



Product
TMS022 1xTL-D36W/840 HFSUK

