



# Lineco TMS022 UK

## TMS022 2xTL-D58W HFSUK

TMS022, 2, MASTER TL-D, 58 W, HF Standard

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

### Product data


<b>General Information</b>	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Product family code	TMS022 [TMS022]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
<b>Light Technical</b>	
Number of light sources	2
Optic type	-
<b>Operating and Electrical</b>	
Input Voltage	230 to 240 V
Power Consumption	58 W
<b>Mechanical and Housing</b>	
Fixation point length distance (nom.)	900 mm

Overall length	1,525 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
<b>Application Conditions</b>	
Suitable for random switching	Not applicable
<b>Product Data</b>	
Order product name	TMS022 2xTL-D58W HFSUK
Full product name	TMS022 2xTL-D58W HFSUK
Full EOC	871155913571700
Order code	13571700
Material no. (12 NC)	910402208503
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711559135717
Numerator – packs per outer box	1

Lineco TMS022 UK

EAN/UPC - Case	8711559135717
----------------	---------------

Dimensional drawing



Product
TMS022 2xTL-D58W HFSUK

