



Lineco TMS022 UK

TMS022 2xTL-D58W/840 HFSUK

TMS022, 2, MASTER TL-D, 58 W, 840 neutral white, HF Standard

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Product data


| | | | |
|---------------------------------|---|---------------------------------------|----------------------------|
| General Information | | Power Consumption | |
| Lamp family code | TL-D [MASTER TL-D] | 58 W | |
| Gear | HFS [HF Standard] | Mechanical and Housing | |
| Product family code | TMS022 [TMS022] | Fixation point length distance (nom.) | 900 mm |
| CE mark | Yes | Overall length | 1,525 mm |
| Flammability mark | For mounting on normally flammable surfaces | Approval and Application | |
| ENEC mark | ENEC mark | Ingress protection code | IP20 [Finger-protected] |
| Glow-wire test | Temperature 650 °C, duration 5 s | Mech. impact protection code | IK02 [0.2 J standard] |
| Light Technical | | Protection class IEC | Safety class I |
| Number of light sources | 2 | Application Conditions | |
| Light source colour | 840 neutral white | Suitable for random switching | Not applicable |
| Optic type | - | Product Data | |
| Operating and Electrical | | Order product name | TMS022 2xTL-D58W/840 HFSUK |
| Input Voltage | 230 to 240 V | Full product name | TMS022 2xTL-D58W/840 HFSUK |

Lineco TMS022 UK

| | |
|-----------------------------------|-----------------|
| Full EOC | 871155913572400 |
| Local code description | TMS25HF |
| Order code | 13572400 |
| Material no. (12 NC) | 910402208603 |
| Local order code | TMS25HF |
| SAP numerator – quantity per pack | 1 |

| | |
|---------------------------------|---------------|
| EAN/UPC – Product/Case | 8711559135724 |
| Numerator – packs per outer box | 1 |
| EAN/UPC – Case | 8711559135724 |

Dimensional drawing



| |
|----------------------------|
| Product |
| TMS022 2xTL-D58W/840 HFSUK |

