



TMS028

TMS028 2xTL-D36W HFS

TMS028, 2, MASTER TL-D, 36 W, HF Standard

TMS028 is a basic batten for 1 or 2 TL-D fluorescent lamps and includes optics for general lighting. It can be suspended or surface-mounted. A lamellae louver, end caps and inline couplers are available as accessories. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps).


Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Feed-through wiring	-
Product family code	TMS028 [TMS028]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	36 W
Connection	-
Mechanical and Housing	
Fixation point length distance (Nom)	960 mm
Overall length	1,232 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMS028 2xTL-D36W HFS
Full product name	TMS028 2xTL-D36W HFS
Full product code	871155913554000
Order code	910402217103
Material Nr. (12NC)	910402217103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559135540
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559135540

TMS028

Dimensional drawing



Product

TMS028 2xTL-D36W HFS

