



# TMS028

## TMS028 2xTL-D58W HFS

TMS028, 2, MASTER TL-D, 58 W, HF Standard


TMS028 is a basic batten for 1 or 2 TL-D fluorescent lamps and includes optics for general lighting. It can be suspended or surface-mounted. A lamellae louver, end caps and inline couplers are available as accessories. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps).

### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Feed-through wiring	-
Product family code	TMS028 [TMS028]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	58 W
Connection	-
Mechanical and Housing	
Fixation point length distance (Nom)	1,260 mm
Overall length	1,532 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMS028 2xTL-D58W HFS
Full product name	TMS028 2xTL-D58W HFS
Full product code	871155913555700
Order code	910402217203
Material Nr. (12NC)	910402217203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559135557
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559135557

Dimensional drawing



Product
TMS028 2xTL-D58W HFS

