



TMS028

TMS028 1xTL-D36W HFS

TMS028, 1, MASTER TL-D, 36 W, HF Standard

TMS028 is a basic batten for 1 or 2 TL-D fluorescent lamps and includes optics for general lighting. It can be suspended or surface-mounted. A lamellae louver, end caps and inline couplers are available as accessories. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps).

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Feed-through wiring	-
Product family code	TMS028 [TMS028]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical

Number of light sources	1
-------------------------	---

Operating and Electrical

Input Voltage	220 to 240 V
Power Consumption	36 W
Connection	-

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Protection class IEC	Safety class I
----------------------	----------------

Application Conditions


Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Order product name	TMS028 1xTL-D36W HFS
Full product name	TMS028 1xTL-D36W HFS
Full product code	872790061101400
Order code	910402217503
Material Nr. (12NC)	910402217503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900611014
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900611014

TMS028

Dimensional drawing



Product
TMS028 1xTL-D36W HFS

