



# Lineco TMS022

## TMS022 2xTL-D58W HF SH

TMS022, 2, MASTER TL-D, 58 W, Electronic high-frequency

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

### Product data


<b>General Information</b>	
Lamp family code	TL-D [MASTER TL-D]
Gear	HF [Electronic high-frequency]
Product family code	TMS022 [TMS022]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
<b>Light Technical</b>	
Number of light sources	2
Optic type	-
<b>Operating and Electrical</b>	
Input Voltage	230 to 240 V
Power Consumption	58 W
<b>Mechanical and Housing</b>	
Fixation point length distance (Nom)	900 mm

Overall length	1,525 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
<b>Application Conditions</b>	
Suitable for random switching	Not applicable
<b>Product Data</b>	
Order product name	TMS022 2xTL-D58W HF SH
Full product name	TMS022 2xTL-D58W HF SH
Full product code	871829104536699
Order code	910402269903
Material Nr. (12NC)	910402269903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291045366
Numerator - Packs per outer box	6

Lineco TMS022

EAN/UPC - Case	8718291044901
----------------	---------------

Dimensional drawing



Product
TMS022 2xTL-D58W HF SH

