



# EFix TCS260

## TCS260 2x49W/830 HFS M6 WH

EFix surface mounted, 2, 49 W, 830 warm white, HF Standard, Matt optic double parabolic louver closed, White

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

### Product data

| General Information |                                             |
|---------------------|---------------------------------------------|
| Lamp family code    | TL5 [TL5]                                   |
| Gear                | HFS [HF Standard]                           |
| Product family code | TCS260 [EFix surface mounted]               |
| Value ladder        | Performance                                 |
| Embedded control    | -                                           |
| CE mark             | Yes                                         |
| Flammability mark   | For mounting on normally flammable surfaces |

| Light Technical          |                                           |
|--------------------------|-------------------------------------------|
| Number of light sources  | 2                                         |
| Light source color       | 830 warm white                            |
| Optic type               | Matt optic double parabolic louver closed |
| Optical cover type       | -                                         |
| Operating and Electrical |                                           |
| Input Voltage            | 220 to 240 V                              |
| Power Consumption        | 49 W                                      |

EFix TCS260

|                                      |                         |
|--------------------------------------|-------------------------|
| Mechanical and Housing               |                         |
| Fixation point length distance (Nom) | 1,300 mm                |
| Housing Color                        | White                   |
| Overall length                       | 1,541 mm                |
| Approval and Application             |                         |
| Ingress protection code              | IP20 [Finger-protected] |
| Protection class IEC                 | Safety class I          |
| Application Conditions               |                         |
| Suitable for random switching        | Not applicable          |

|                                 |                            |
|---------------------------------|----------------------------|
| Product Data                    |                            |
| Order product name              | TCS260 2x49W/830 HFS M6 WH |
| Full product name               | TCS260 2x49W/830 HFS M6 WH |
| Full product code               | 872790061147200            |
| Order code                      | 910402377512               |
| Material Nr. (12NC)             | 910402377512               |
| Numerator - Quantity Per Pack   | 1                          |
| EAN/UPC - Product/Case          | 8727900611472              |
| Numerator - Packs per outer box | 1                          |
| EAN/UPC - Case                  | 8727900611472              |

Dimensional drawing



| Product                    | A        | B      | C        |
|----------------------------|----------|--------|----------|
| TCS260 2x49W/830 HFS M6 WH | 1,300 mm | 650 mm | 1,541 mm |

