

# EFix TPS262

## TPS262 2x80W/840 HFP D6 SMT SI

EFix suspended mounted, 2, 80 W, 840 neutral white, HF Performer, Semi-high-gloss optic double parabolic, Silver

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

### Product data

| General Information |   |
|---------------------|---|
| Lamp family code    | TL5 [TL5]                                   |
| Gear                | HFP [HF Performer]                          |
| Service tag         | Yes   |
| Product family code | TPS262 [EFix suspended mounted]             |
| Embedded control    | -   |
| CE mark             | Yes   |
| Flammability mark   | For mounting on normally flammable surfaces |
| ENEC mark           | ENEC mark                                   |

| Glow-wire test           | Temperature 850 °C, duration 5 s       |
|--------------------------|--|
| Light Technical          |  |
| Number of light sources  | 2                                      |
| Light source color       | 840 neutral white                      |
| Optic type               | Semi-high-gloss optic double parabolic |
| Optical cover type       | -                                      |
| Operating and Electrical |  |
| Input Voltage            | 220 to 240 V                           |

EFix TPS262

|                   |      |
|-------------------|------|
| Power Consumption | 80 W |
| Cable             | -    |

Mechanical and Housing

|                |          |
|----------------|----------|
| Housing Color  | Silver   |
| Overall length | 1,541 mm |

Approval and Application



|                         |                         |
|-------------------------|-------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Protection class IEC    | Safety class I          |

Application Conditions

|                               |                |
|-------------------------------|----------------|
| Suitable for random switching | Not applicable |
|-------------------------------|----------------|

|                                 |                                |
|---------------------------------|--------------------------------|
| Product Data                    |                                |
| Order product name              | TPS262 2x80W/840 HFP D6 SMT SI |
| Full product name               | TPS262 2x80W/840 HFP D6 SMT SI |
| Full product code               | 872790061423700                |
| Order code                      | 910402469112                   |
| Material Nr. (12NC)             | 910402469112                   |
| Numerator - Quantity Per Pack   | 1                              |
| EAN/UPC - Product/Case          | 8727900614237                  |
| Numerator - Packs per outer box | 1                              |
| EAN/UPC - Case                  | 8727900614237                  |

Dimensional drawing



| Product                        | B      | C        |
|--------------------------------|--------|----------|
| TPS262 2x80W/840 HFP D6 SMT SI | 650 mm | 1,541 mm |

