



# TCW060

## TCW060 1xTL-D58W HFP

TCW060, 1, MASTER TL-D, 58 W, HF Performer

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

### Product data


<b>General Information</b>	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFP [HF Performer]
Service tag	Yes
Product family code	TCW060 [TCW060]
CE mark	Yes
Glow-wire test	Temperature 650 °C, duration 5 s
<b>Light Technical</b>	
Number of light sources	1
Optical cover type	Polycarbonate bowl/cover prismatic
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Power Consumption	58 W
Connection	Screw connection block 3-pole
<b>Mechanical and Housing</b>	
Fixation point length distance (Nom)	1,200 mm

Housing Color	Grey
Overall length	1,570 mm
<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
<b>Application Conditions</b>	
Suitable for random switching	Yes
<b>Product Data</b>	
Order product name	TCW060 1xTL-D58W HFP
Full product name	TCW060 1xTL-D58W HFP
Full product code	872790063863900
Order code	910402498712
Material Nr. (12NC)	910402498712
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900638639
Numerator - Packs per outer box	1

TCW060

EAN/UPC - Case	8727900638639
----------------	---------------

Dimensional drawing



Product	A	B
TCW060 1xTL-D58W HFP	1,200 mm	1,570 mm

