



TCW060

TCW060 2xTL-D18W HFP

TCW060, 2, MASTER TL-D, 18 W, HF Performer

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data


General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFP [HF Performer]
Service tag	Yes
Product family code	TCW060 [TCW060]
CE mark	Yes
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Number of light sources	2
Optical cover type	Polycarbonate bowl/cover prismatic
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	18 W
Connection	Screw connection block 3-pole
Mechanical and Housing	
Fixation point length distance (Nom)	350 mm

Housing Color	Grey
Overall length	660 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Application Conditions	
Suitable for random switching	Yes
Product Data	
Order product name	TCW060 2xTL-D18W HFP
Full product name	TCW060 2xTL-D18W HFP
Full product code	872790063867700
Order code	910402499112
Material Nr. (12NC)	910402499112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900638677
Numerator - Packs per outer box	1

TCW060

EAN/UPC - Case	8727900638677
----------------	---------------

Dimensional drawing



Product	A	B
TCW060 2xTL-D18W HFP	350 mm	660 mm

