



Pacific TCW216

TCW216 2xTL-D36W HFS EL1 PI

PACIFIC, 2, MASTER TL-D, 36 W, HF Performer, Emergency lighting 1 hour duration, Push-in connector 3-pole

Pacific TCW216 is a functional dust-, jet-, shock- and vandalproof luminaire, and can accommodate both TL-D and TL5 (16 mm) fluorescent lamps. The cover is fixed to the housing by means of an innovative concept using integrated fixing points to avoid external lockers. There is a choice of different standard versions available. The luminaire can be mounted individually or in-line with easy 'click' installation. Flexibility is ensured with a choice of fixing points and different cable entries. The TCW216 can also be suspended from Philips TTX410 light-line systems.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Light source replaceable	Yes
Gear	HFP [HF Performer]
Driver included	Yes
Feed-through wiring	-
Product family code	TCW216 [PACIFIC]
Explosion hazard class	-
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2


Optic type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	36 W
Connection	Push-in connector 3-pole
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Polyester
Fixation point length distance (Nom)	600 mm
Overall length	1,300 mm

Pacific TCW216

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCW216 2xTL-D36W HFS EL1 PI

Full product name	TCW216 2xTL-D36W HFS EL1 PI
Full product code	871155929330100
Order code	910402615918
Material Nr. (12NC)	910402615918
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559293301
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559293301

Dimensional drawing



Product	A	B
TCW216 2xTL-D36W HFS EL1 PI	925 mm	1,300 mm

