



# Pacific TCW216

## ZCW216 LOC-VP (6PCS)

Pacific TCW216, Accessory

Functional shock-, vandal-, dust-, and jetproof luminaire for TL-D and TL5 fluorescent lamps. Fibre-glass reinforced polyester housing with a polycarbonate prismatic clear cover. Fixation of the cover to the housing without additional lockers, but by innovative concept with integrated fixation points. Gear tray, 2 stainless steel ceiling fixation clips and cable entries (membranes) supplied with the luminaire. Choice of different standard versions available: versions 1/2 x 18W, 1/2 x 36W, 1/2 x 58W (TL-D) and 1/2 x 49W (TL5), emergency lighting, 1- or 3 hours, ready-to-install, including lamp(s) and Waterproof External Connector (WEC), equipped with through-wiring 5 x 2.5 mm<sup>2</sup>.

### Product data

Approval and Application	
Protection class IEC	-

  

Product Data	
Order product name	ZCW216 LOC-VP (6PCS)
Full product name	ZCW216 LOC-VP (6PCS)
Full product code	871155929395099
Order code	29395099

  

Material Nr. (12NC)	910402621518
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559293950
Numerator - Packs per outer box	50
EAN/UPC - Case	8711559293967