



# TTX400 TL5, TMX400 electrical units

## TMX400 2xTL5-49W HFR-TD

TTX400, 2, TL5, 49 W, HF Regulator touch-switch dimming DALI interface

These electrical units are designed for quick click mounting in TTX400 trunking sections. They are for use with one or two TL5 lamps, with electronic (dimming) ballast, in emergency lighting version and in versions for the mounting of projectors. They contain all the necessary electrical and mechanical functions. All components are screwed onto the electrical unit. The units can be combined with any type of reflector and are made of white sheet steel. Electronic ballasts – TMX400 is delivered with electronic ballast HFP. The dimmable version of the TMX400 is delivered with the electronic ballast HFR, allowing the light output of the TL5 lamps to be regulated from 3 to 100 %. This unit is ideal for (day)light-dependent control and must be mounted to the prewired TTX400 section with 7-wire ribbon cable. For more control options the TMX400 can be equipped with DALI ballasts. Especially in combination with the Linesense controls DALI solutions offer even more control and energy savings. Emergency lighting – TMX400 is deliverable in versions with built in 3-hour or 1-hour emergency lighting equipment. For configuration of both emergency lighting and regulation or DALI, TTX400 9-wires is to be used with TMX400 9. New solution of standard TTX400 7-wires with new units TMX400 C-2R is recommended.

### Product data

General Information			
Lamp family code	TL5 [TL5]	CE mark	Yes
Gear	HF Regulator touch-switch dimming DALI interface	ENEC mark	ENEC mark
Product family code	TMX400 [TTX400]		

## TTX400 TL5, TMX400 electrical units

### Light Technical

Number of light sources	2
-------------------------	---

### Operating and Electrical

Power Consumption	49 W
Connection	-

### Mechanical and Housing

Overall length	1,474 mm
----------------	----------

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I



### Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

### Product Data

Order product name	TMX400 2xTL5-49W HFR-TD
Full product name	TMX400 2xTL5-49W HFR-TD
Full product code	871155930333899
Order code	910402641918
Material Nr. (12NC)	910402641918
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559303338
Numerator - Packs per outer box	2
EAN/UPC - Case	8711559303345

## Dimensional drawing



### Product

TMX400 2xTL5-49W HFR-TD

