



ComfortVision SNF111

SNF111 2xHPI-TP400W K NB

COMFORTVISION, 2, MASTER HPI-T Plus, 400 W, Narrow beam

ComfortVision is a high-efficiency, asymmetric floodlight, distributing a low-glare beam evenly and accurately. It can accommodate metal-halide lamps for good color rendering or a high-pressure sodium lamp for economical performance. Available in medium- or narrow-beam versions, the floodlight accepts a single 1000 or two 400 or 600 W lamps. The twin-lamp version offers switching flexibility that permits tailoring to the user's needs while allowing energy savings. ComfortVision's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing. For optimal downlighting, the luminaire should be mounted horizontally at a height of 15–25 meters. It has an adjustment range of $\pm 12^\circ$ from the horizontal. A universal mounting bracket allows mounting to headframes, ceilings and walls.

Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Gear	CONV [Conventional]
Product family code	SNF111 [COMFORTVISION]
CE mark	Yes
ENEC mark	-
Light Technical	
Number of light sources	2
Optic type outdoor	Narrow beam
Operating and Electrical	
Power Consumption	400 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Protection class IEC	Safety class I
Product Data	
Order product name	SNF111 2xHPI-TP400W K NB
Full product name	SNF111 2xHPI-TP400W K NB
Full product code	871155954756500
Order code	910403029612
Material Nr. (12NC)	910403029612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559547565
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559547565

Dimensional drawing

