



DecoScene DBP522

DBP522 CDM-T70W/830 I MB GR RMR

Decoscene Medium, MASTERColour CDM-T, 70 W, Medium beam

DecoScene is a ground-recessed uplighter for enhancing, highlighting or even revealing the architecture of the city at night. An unobtrusive presence by day, DecoScene offers a wide choice of light sources, beams, adjustment possibilities and accessories to deliver the optimum upward lighting effect after dark, e.g. to illuminate monuments, highlight a striking piece of architecture or mark out a luminous path through a park or garden. The DecoScene range, comprising three conventional versions (DBP521, DBP522 and DBP523) and one LED version (BBP521), complies with the CEI 60598-2-13 norm and offers a glass temperature below 80°C. A wide choice of accessories is available, e.g. for enhanced guidance.

Product data

General Information		Optic type outdoor	
Lamp family code	CDM-T [MASTERColour CDM-T]	Medium beam	
Light source replaceable	Yes	Operating and Electrical	
Gear	CONV [Conventional]	Input Voltage	230 V
Driver included	Yes	Line Frequency	50 Hz
Product family code	DBP522 [Decoscene Medium]	Power Consumption	70 W
CE mark	Yes	Cable	-
Light Technical		Controls and Dimming	
Color rendering index (CRI)	84	Dimmable	No
Number of light sources	1	Driver/power unit/transformer	-
Light source color	830 warm white	Mechanical and Housing	
Optical cover type	Clear glass	Housing Color	Grey

DecoScene DBP522

Mounting device	Recessed mounting box round
Approval and Application	
Protection class IEC	Safety class I
Product Data	
Full product code	871155972782000
Order product name	DBP522 CDM-T70W/830 I MB GR RMR
Order code	910403096812

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910403096812
Full product name	DBP522 CDM-T70W/830 I MB GR RMR
EAN/UPC - Case	8711559727820
EAN/UPC - Product/Case	8711559727820

Dimensional drawing

