



# SmartForm TBS460

## ZBS460 SMB-TPM (1 set = 4PCS)

### TBS460 ACC

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in square and rectangular versions. Designed to fit in a wide range of ceiling types, SmartForm can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m<sup>2</sup> is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO<sub>2</sub> levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS460 – ultra-flat 'light beam'. SmartForm recessed TBS460 'light beam' luminaires are built around superior micro-optics and have a build-in height of a mere 45 mm, making them ideal for applications requiring very flat light fittings, e.g. refurbishment projects where ceiling space may be especially limited.

### Product data

General Information		Material Nr. (12NC)	
Product family code	ZBS460 [TBS460 ACC]	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8711559493039
Order product name	ZBS460 SMB-TPM (1 set = 4PCS)	Numerator - Packs per outer box	50
Full product name	ZBS460 SMB-TPM (1 set = 4PCS)	EAN/UPC - Case	8711559493046
Full product code	871155949303999		
Order code	910403202603		