



# SmartForm TBS417

## ZBS417 EP-S RAL9010 SET

### TBS415 ACC

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m<sup>2</sup> is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO<sub>2</sub> levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

### Product data

| General Information |                         |                                 |               |
|---------------------|-------------------------|---------------------------------|---------------|
| Accessory color     | -                       | Order code                      | 910403205303  |
| Product family code | ZBS417 [TBS415 ACC]     | Material Nr. (12NC)             | 910403205303  |
|                     |                         | Numerator - Quantity Per Pack   | 1             |
|                     |                         | EAN/UPC - Product/Case          | 8717943984565 |
|                     |                         | Numerator - Packs per outer box | 20            |
|                     |                         | EAN/UPC - Case                  | 8717943984572 |
| Product Data        |                         |                                 |               |
| Order product name  | ZBS417 EP-S RAL9010 SET |                                 |               |
| Full product name   | ZBS417 EP-S RAL9010 SET |                                 |               |
| Full product code   | 871794398456599         |                                 |               |