



SmartForm TBS417

ZBS417 EP-A RAL9010 SET

TBS415 ACC

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

Product data

General Information			
Accessory color	-	Order code	910403205503
Product family code	ZBS417 [TBS415 ACC]	Material Nr. (12NC)	910403205503
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8717943984602
		Numerator - Packs per outer box	20
		EAN/UPC - Case	8717943984619
Product Data			
Order product name	ZBS417 EP-A RAL9010 SET		
Full product name	ZBS417 EP-A RAL9010 SET		
Full product code	871794398460299		