



Pacific II TCW097

TCW097 1xTL5-14W HF 220V 50Hz

1, TL5, 14 W, Electronic economy, 220 V, 50 Hz

Functional impact-, dust- and jetproof luminaire for single and twin TLD and TL5 fluorescent lamps for indoor applications and semioutdoor applications. Housing and cover of TCW097 are made of high quality poly-carbonate which has an excellent impact resistant property. The cover has anti-UV additives which bring additional performance levels to UV protection. Available with conventional or high-frequency (HF) electronic control gears. Can be ceiling mounted or suspended. Equipped with mounting brackets, mounting is made easy via screws without drilling into the luminaire housing. Gear tray and metal toggles are re-installed; cable gland and mounting brackets are delivered with the luminaire.


Product data

General Information	
Lamp family code	TL5 [TL5]
Number of gear units	1 unit
Gear	EBE [Electronic economy]
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	14 W
Approval and Application	
Ingress protection code	-

Protection class IEC	Safety class I
Product Data	
Order product name	TCW097 1xTL5-14W HF 220V 50Hz
Full product name	TCW097 1xTL5-14W HF 220V 50Hz
Full product code	910403358480
Order code	910403358480
Material Nr. (12NC)	910403358480
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Pacific II TCW097

Dimensional drawing



TCW097	118 114	136 128	158 135	218 214	236 228	258 235
LxWxH(mm)	660x100x110	1270x100x110	1570x100x110	660x150x110	1270x150x110	1570x150x110

