



Sereno TBS869/528

TBS528 2xTL5-14W HF M2 IPP

2, TL5, 14 W, Electronic economy, Matt mirror ribbed lamellae louver

The new Philips range Sereno recessed luminaires are more energy efficient than ever before. The latest optical technology was used to create a highly effective optic, giving rise to new opportunities for saving energy. This family of advanced TL5 recessed luminaire with micro optic technology use up to 25% less energy than standard TL5 solutions. Even greater savings can be made by retrofitting TLD lighting installations with our new TL5 recessed luminaires. The quality of the lighting is maintained, thanks to the Omni directional Lighting Control optic which increases luminous efficacy while reducing glare in all directions and complying with relevant brightness limits. As a result, our luminaires enable sustainable and green lighting solutions to be created. Because daylight-linking and presence-detecting lighting control systems can be optionally packaged into your recessed luminaire lighting solution, your energy consumption can easily be halved in comparison to conventional office lighting solutions.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EBE [Electronic economy]

Light Technical	
Number of light sources	2
Light source color	-
Optic type	Matt mirror ribbed lamellae louver

Operating and Electrical	
Power Consumption	14 W
Cable	-

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Order product name	TBS528 2xTL5-14W HF M2 IPP
Full product name	TBS528 2xTL5-14W HF M2 IPP

Sereno TBS869/528

Full product code	910403392701
Order code	910403392701
Material Nr. (12NC)	910403392701
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	2
---------------------------------	---

Dimensional drawing

