



# Sereno TBS869/528

## TBS528 4xTL5-14W HFP M2 FU IPP

4, TL5, 14 W, Electronic Primalume, Matt mirror ribbed lamellae louver, Fuse included

The new Philips range Sereno recessed luminaires are more energy efficient than ever before. The latest optical technology was used to create a highly effective optic, giving rise to new opportunities for saving energy. This family of advanced TL5 recessed luminaire with micro optic technology use up to 25% less energy than standard TL5 solutions. Even greater savings can be made by retrofitting TLD lighting installations with our new TL5 recessed luminaires. The quality of the lighting is maintained, thanks to the Omni directional Lighting Control optic which increases luminous efficacy while reducing glare in all directions and complying with relevant brightness limits. As a result, our luminaires enable sustainable and green lighting solutions to be created. Because daylight-linking and presence-detecting lighting control systems can be optionally packaged into your recessed luminaire lighting solution, your energy consumption can easily be halved in comparison to conventional office lighting solutions.

### Product data

General Information		Operating and Electrical	
Lamp family code	TL5 [TL5]	Power Consumption	14 W
Gear	EBP [Electronic Primalume]	Cable	-
Light Technical		Approval and Application	
Number of light sources	4	Ingress protection code	IP20 [Finger-protected]
Light source color	-	Product Data	
Optic type	Matt mirror ribbed lamellae louver	Order product name	TBS528 4xTL5-14W HFP M2 FU IPP
		Full product name	TBS528 4xTL5-14W HFP M2 FU IPP

Sereno TBS869/528

Full product code	910403395901
Order code	910403395901
Material Nr. (12NC)	910403395901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163285757

Numerator - Packs per outer box	2
EAN/UPC - Case	8710163285757

Dimensional drawing

