



Celino TPS680 C

TPS680 C 1xTL5-35W HFP AC-MLO FU SM2 ALU

1, TL5, 35 W, HF Performer, Acrylate micro-lens optic, Fuse included, Aluminum

Celino is a complete luminaire range that reflects the market trend towards miniaturization and architectural integration, while at the same time delivering a significant advance in optical performance. Celino features Philips' aluminum micro optic with 3D lamellae, which ensures optimum visual comfort and efficiency in compliance with the latest office-lighting norm (EN 12464-1). Made of natural anodized aluminum, the housing of Celino is a mere 71 mm wide and has die-cast-aluminum end caps. The design allows multiple luminaires to be connected in a line arrangement. Celino is available as a full range – suspended, surface-mounted, free-standing, recessed and wall-mounted – for maximum freedom in application.


Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Light Technical	
Number of light sources	1
Optic type	-
Optical cover type	Acrylate micro-lens optic
Operating and Electrical	
Power Consumption	35 W
Mechanical and Housing	
Housing Color	Aluminum

Product Data	
Order product name	TPS680 C 1xTL5-35W HFP AC-MLO FU SM2 ALU
Full product name	TPS680 C 1xTL5-35W HFP AC-MLO FU SM2 ALU
Full product code	910403630041
Order code	910403630041
Material Nr. (12NC)	910403630041
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Celino TPS680 C

Dimensional drawing



Product	A	B
TPS680 C 1xTL5-35W HFP AC-MLO FU SM2 ALU	1,520 mm	1,420 mm

