

Celino TPS680 C

TPS680 C 2xTL5-35W HFP D8 FU SM2 ALU

2, TL5, 35 W, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Fuse included, Aluminum

Celino is a complete luminaire range that reflects the market trend towards miniaturization and architectural integration, while at the same time delivering a significant advance in optical performance. Celino features Philips’ aluminum micro optic with 3D lamellae, which ensures optimum visual comfort and efficiency in compliance with the latest office-lighting norm (EN 12464-1). Made of natural anodized aluminum, the housing of Celino is a mere 71 mm wide and has die-cast-aluminum end caps. The design allows multiple luminaires to be connected in a line arrangement. Celino is available as a full range – suspended, surface-mounted, free-standing, recessed and wall-mounted – for maximum freedom in application.


Product data

| General Information | |
|--------------------------|---|
| Lamp family code | TL5 [TL5] |
| Gear | HFP [HF Performer] |
| Light Technical | |
| Number of light sources | 2 |
| Optic type | Semi-high-gloss optic 3D micro-lamellae |
| Optical cover type | - |
| Operating and Electrical | |
| Power Consumption | 35 W |
| Mechanical and Housing | |
| Housing Color | Aluminum |

| Product Data | |
|---------------------------------|--------------------------------------|
| Order product name | TPS680 C 2xTL5-35W HFP D8 FU SM2 ALU |
| Full product name | TPS680 C 2xTL5-35W HFP D8 FU SM2 ALU |
| Full product code | 910403630048 |
| Order code | 910403630048 |
| Material Nr. (12NC) | 910403630048 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Celino TPS680 C

Dimensional drawing



| Product | A | B |
|--------------------------------------|----------|----------|
| TPS680 C 2xTL5-35W HFP D8 FU SM2 ALU | 1,520 mm | 1,108 mm |

