



# FBH/FBS145 C

## FBH145 C 2xPL-C/4P18W HFP WH

China - 2 pcs - MASTER PL-C 4 Pin - 18 W - Electronic Primalume - White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.


### Product data

General Information	
Duplication code	C [ China]
Number of light sources	2 [ 2 pcs]
Lamp family code	PL-C/4P [ MASTER PL-C 4 Pin]
Lamp power	18 W
Gear	EBP [ Electronic Primalume]
Driver/power unit/transformer	No [-]
Optical cover/lens type	No [-]
Country version	NO [ Norway]
Operating and Electrical	
Input voltage	220 V
Input frequency	50 Hz

Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Product Data	
Full product code	910403630232
Order product name	FBH145 C 2xPL-C/4P18W HFP WH
Order code	03630232
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910403630232
Net weight (piece)	1.150 kg

FBH/FBS145 C

Dimensional drawing



FBH/FBS145 C

