



# FBH/FBS145 C

## FBH145 C 2xPL-C/2P26W I WH

China - 2 pcs - MASTER PL-C 2 Pin - 26 W - Inductive - White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

### Product data

General Information	
Duplication code	C [ China]
Number of light sources	2 [ 2 pcs]
Lamp family code	PL-C/2P [ MASTER PL-C 2 Pin]
Lamp power	26 W
Compensation circuit	Inductive
Gear	CONV [ Conventional]
Driver/power unit/transformer	No [ -]
Optical cover/lens type	No [ -]
Country version	NO [ Norway]

Operating and Electrical	
Input voltage	220 V
Input frequency	50 Hz


Approval and Application	
Ingress protection code	IP20 [ Finger-protected]

Product Data	
Full product code	910403630233
Order product name	FBH145 C 2xPL-C/2P26W I WH
Order code	910403630233
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910403630233
Net weight (piece)	3.000 kg

## FBH/FBS145 C

### Dimensional drawing



FBS145 C

