



FBH/FBS145 C

FBH145 C 2xPL-C/4P26W HFP WH

2, MASTER PL-C 4 Pin, 26 W, Electronic Primalume, White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	EBP [Electronic Primalume]
Light Technical	
Number of light sources	2
Optical cover type	-
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	26 W
Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FBH145 C 2xPL-C/4P26W HFP WH
Full product name	FBH145 C 2xPL-C/4P26W HFP WH
Full product code	910403630236
Order code	910403630236
Material Nr. (12NC)	910403630236
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291994312
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291994312

FBH/FBS145 C

Dimensional drawing

