



Smart Halogen Downlight QBS020

QBS020 1x MAX35W/12V-GU4 WH

1, GU4, White

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

Product data

General Information		Temperature	
Cap-Base	GU4 [GU4]	Ambient temperature range	-10 to +35 °C
Lighting Technology	LED	Mechanical and Housing	
Light Technical		Housing Color	White
Number of light sources	1	Overall length	85 mm
Luminaire light beam spread	108°	Overall width	300 mm
Operating and Electrical		Overall height	300 mm
Input Voltage	12 V	Dimensions (Height x Width x Depth)	300 x 300 x 85 mm
Line Frequency	50 to 60 Hz	Approval and Application	
Input Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.3 J]
		Protection class IEC	Safety class II

Smart Halogen Downlight QBS020

Product Data	
Order product name	QBS020 1x MAX35W/12V-GU4 WH
Full product name	QBS020 1x MAX35W/12V-GU4 WH
Full product code	910403630255
Order code	910403630255
Material Nr. (12NC)	910403630255

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687410
Numerator - Packs per outer box	100
EAN/UPC - Case	6923828698966

Dimensional drawing

