



Smart Halogen Downlight QBS020

QBS021 1x MAX35W/12V-GU4 WH

1, GU4, White

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

Product data

General Information	
Cap-Base	GU4 [GU4]
Lighting Technology	LED
Light Technical	
Number of light sources	1
Luminaire light beam spread	108°
Operating and Electrical	
Input Voltage	12 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Temperature	
Ambient temperature range	-10 to +35 °C
Mechanical and Housing	
Housing Color	White
Overall length	75 mm
Overall width	322 mm
Overall height	322 mm
Dimensions (Height x Width x Depth)	322 x 322 x 75 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

Smart Halogen Downlight QBS020

Product Data	
Order product name	QBS021 1x MAX35W/12V-GU4 WH
Full product name	QBS021 1x MAX35W/12V-GU4 WH
Full product code	910403630257
Order code	910403630257
Material Nr. (12NC)	910403630257

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687434
Numerator - Packs per outer box	100
EAN/UPC - Case	6923828698980

Dimensional drawing

