



# Smart Halogen Downlight QBS020

## QBS022 1x MAX50W/12V-GU5.3 WH

1, GU5.3, White

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

### Product data

General Information		Temperature	
Cap-Base	GU5.3 [GU5.3]	Ambient temperature range	-10 to +35 °C
Lighting Technology	LED		
Light Technical		Mechanical and Housing	
Number of light sources	1	Housing Color	White
Luminaire light beam spread	108°	Overall length	85 mm
		Overall width	300 mm
		Overall height	300 mm
		Dimensions (Height x Width x Depth)	300 x 300 x 85 mm
Operating and Electrical		Approval and Application	
Input Voltage	12 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 to 60 Hz	Mech. impact protection code	IK03 [0.3 J]
Input Frequency	50 to 60 Hz	Protection class IEC	Safety class II

# Smart Halogen Downlight QBS020

## Product Data

Order product name	QBS022 1x MAX50W/12V-GU5.3 WH
Full product name	QBS022 1x MAX50W/12V-GU5.3 WH
Full product code	910403630259
Order code	03630259
Material Nr. (12NC)	910403630259

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687458
Numerator - Packs per outer box	50
EAN/UPC - Case	6923828699000

## Dimensional drawing

