



Tango 4 MVP483

MVP483 SON-T1000W H 220-240V A-NB

SON-T, 1000 W, External gear box, Asymmetrical narrow beam

Tango 4 is a high wattage flood luminaire for up to 1000W SON-T and HPI-T lamps with symmetrical and asymmetrical reflectors. It is ideally suited to a variety of outdoor applications – from architectural, facade and billboard lighting to area and (recreational) sports lighting. The Tango 4 compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. Access to the lamp and gear is quick and easy, via the hinged front glass with its quick-release stainless-steel clips. Tango 4 luminaires are RoHS compliant.

Product data

General Information		Full product name	MVP483 SON-T1000W H 220-240V A-NB
Lamp family code	SON-T [SON-T]	Full product code	910403630303
Gear	H [External gear box]	Order code	910403630303
Light Technical		Material Nr. (12NC)	910403630303
Optic type outdoor	Asymmetrical narrow beam	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	6923828601881
Input Voltage	220 to 240 V	Numerator - Packs per outer box	1
Power Consumption	1,000 W	EAN/UPC - Case	6923828601881
Product Data			
Order product name	MVP483 SON-T1000W H 220-240V A-NB		

Tango 4 MVP483

Dimensional drawing

