



Tango 4 MVP483

MVP483 HPI-T1000W H 220-240V A-NB

HPI-T High Wattage, 1000 W, External gear box, Asymmetrical narrow beam

Tango 4 is a high wattage flood luminaire for up to 1000W SON-T and HPI-T lamps with symmetrical and asymmetrical reflectors. It is ideally suited to a variety of outdoor applications – from architectural, facade and billboard lighting to area and (recreational) sports lighting. The Tango 4 compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. Access to the lamp and gear is quick and easy, via the hinged front glass with its quick-release stainless-steel clips. Tango 4 luminaires are RoHS compliant.

Product data

General Information		Full product name		MVP483 HPI-T1000W H 220-240V A-NB
Lamp family code	HPI-T [HPI-T High Wattage]	Full product code		910403630305
Gear	H [External gear box]	Order code		910403630305
Light Technical		Material Nr. (12NC)		910403630305
Optic type outdoor	Asymmetrical narrow beam	Numerator - Quantity Per Pack		1
Operating and Electrical		EAN/UPC - Product/Case		6923828601904
Input Voltage	220 to 240 V	Numerator - Packs per outer box		1
Power Consumption	1,000 W	EAN/UPC - Case		6923828601904
Product Data				
Order product name	MVP483 HPI-T1000W H 220-240V A-NB			

Tango 4 MVP483

Dimensional drawing

