



# Tango 4 MVP483

## MVP483 HPI-T1000W H 220-240V S-WB

HPI-T High Wattage, 1000 W, External gear box, Symmetrical wide beam

Tango 4 is a high wattage flood luminaire for up to 1000W SON-T and HPI-T lamps with symmetrical and asymmetrical reflectors. It is ideally suited to a variety of outdoor applications – from architectural, facade and billboard lighting to area and (recreational) sports lighting. The Tango 4 compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. Access to the lamp and gear is quick and easy, via the hinged front glass with its quick-release stainless-steel clips. Tango 4 luminaires are RoHS compliant.

### Product data

<b>General Information</b>		<b>Full product name</b>	MVP483 HPI-T1000W H 220-240V S-WB
Lamp family code	HPI-T [HPI-T High Wattage]	Full product code	910403630312
Gear	H [External gear box]	Order code	910403630312
<b>Light Technical</b>		Material Nr. (12NC)	910403630312
Optic type outdoor	Symmetrical wide beam	Numerator - Quantity Per Pack	1
<b>Operating and Electrical</b>		EAN/UPC - Product/Case	6923828601973
Input Voltage	220 to 240 V	Numerator - Packs per outer box	1
Power Consumption	1,000 W	EAN/UPC - Case	6923828601973
<b>Product Data</b>			
Order product name	MVP483 HPI-T1000W H 220-240V S-WB		

# Tango 4 MVP483

## Dimensional drawing

