



Tango 4 MVP483

MVP483 2xSON-T400W H 220-240V S-WB

2, SON-T, 400 W, External gear box, Symmetrical wide beam

Tango 4 is a high wattage flood luminaire for up to 1000W SON-T and HPI-T lamps with symmetrical and asymmetrical reflectors. It is ideally suited to a variety of outdoor applications – from architectural, facade and billboard lighting to area and (recreational) sports lighting. The Tango 4 compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. Access to the lamp and gear is quick and easy, via the hinged front glass with its quick-release stainless-steel clips. Tango 4 luminaires are RoHS compliant.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	H [External gear box]
Light Technical	
Number of light sources	2
Optic type outdoor	Symmetrical wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	400 W

Product Data	
Order product name	MVP483 2xSON-T400W H 220-240V S-WB
Full product name	MVP483 2xSON-T400W H 220-240V S-WB
Full product code	910403630314
Order code	910403630314
Material Nr. (12NC)	910403630314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828601997
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828601997

Tango 4 MVP483

Dimensional drawing

