



# Basic Modular LBX300

## LBX300 3xMAX50W/12V-GU5.3 GR

Grey

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

### Product data

General Information	
Light source replaceable	No
Gear	-
Lighting Technology	LED
Light Technical	
Luminous Flux	300 lm
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Light source color	3000/4000/6500
Luminaire light beam spread	110°
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	4 W

Power Factor (Fraction)		0.8
Temperature		
Ambient temperature range		0 to +35 °C
Mechanical and Housing		
Housing Material		Plastic
Reflector material		Polycarbonate
Housing Color		Grey
Overall length		225 mm
Overall width		225 mm
Overall height		225 mm
Overall diameter		225 mm
Dimensions (Height x Width x Depth)		225 x 225 x 225 mm
Approval and Application		
Ingress protection code		IP20 [Finger-protected]

# Basic Modular LBX300

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Product Data	
Order product name	LBX300 3xMAX50W/12V-GU5.3 GR
Full product name	LBX300 3xMAX50W/12V-GU5.3 GR
Full product code	910403630430
Order code	03630430

Material Nr. (12NC)	910403630430
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828688233
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828699789

## Dimensional drawing

