



# Theta FBS110

## FBS113 MAX15W-E27 220V

E27, 220 V

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

### Product data

<b>General Information</b>	
Cap-Base	E27 [E27]
Gear	-
Lighting Technology	LED
<b>Light Technical</b>	
Number of light sources	1
Luminaire light beam spread	108°
<b>Operating and Electrical</b>	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
<b>Temperature</b>	
Ambient temperature range	-10 to +35 °C
<b>Mechanical and Housing</b>	
Housing Color	White
Overall length	85 mm
Overall width	300 mm

Overall height	300 mm
Dimensions (Height x Width x Depth)	300 x 300 x 85 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

### Product Data

Order product name	FBS113 MAX15W-E27 220V
Full product name	FBS113 MAX15W-E27 220V
Full product code	910403630460
Order code	910403630460
Material Nr. (12NC)	910403630460
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828688554
Numerator - Packs per outer box	36
EAN/UPC - Case	6923828601294

Theta FBS110

Dimensional drawing

