



# Theta FBS110

## FBS111 MAX15W-E27 220-240V

E27, 220 to 240 V

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

### Product data

General Information	
Cap-Base	E27 [E27]
Gear	-
Lighting Technology	LED
Light Technical	
Number of light sources	1
Luminaire light beam spread	108°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Temperature	
Ambient temperature range	-10 to +35 °C
Mechanical and Housing	
Housing Color	White
Overall length	75 mm
Overall width	322 mm

Overall height	322 mm
Dimensions (Height x Width x Depth)	322 x 322 x 75 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

Product Data	
Order product name	FBS111 MAX15W-E27 220-240V
Full product name	FBS111 MAX15W-E27 220-240V
Full product code	910403630466
Order code	910403630466
Material Nr. (12NC)	910403630466
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163288994
Numerator - Packs per outer box	16
EAN/UPC - Case	8710163289045

Theta FBS110

Dimensional drawing

