



# ProLux TPS550 C

## TPS550 6XTL5-54W HFP NB

6, TL5, 54 W, HF Performer, Narrow beam

In industry, the bottom line is affected by a whole host of factors – worker productivity, running costs and maintenance, to name just a few. In today's economic environment, with margins under pressure, all businesses operating high-bay facilities are faced with the pressing need to save energy. Our ProLux high-bay solution is a direct replacement for current HID high-bay systems and enables significant energy savings. The combination of robust housing, high-reflectance material and specially designed reflector add up to a high-efficiency luminaire that can help drive profitability by improving energy efficiency.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Light Technical	
Number of light sources	6
Optic type	Narrow beam
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	54 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	TPS550 6XTL5-54W HFP NB
Full product name	TPS550 6XTL5-54W HFP NB
Full product code	910403630503
Order code	910403630503
Material Nr. (12NC)	910403630503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291994404
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291994404

## ProLux TPS550 C

### Dimensional drawing

