



# ProLux TPS550 C

## TPS550 2XTL5-54W HFP MB

2, TL5, 54 W, HF Performer, Medium beam

In industry, the bottom line is affected by a whole host of factors – worker productivity, running costs and maintenance, to name just a few. In today's economic environment, with margins under pressure, all businesses operating high-bay facilities are faced with the pressing need to save energy. Our ProLux high-bay solution is a direct replacement for current HID high-bay systems and enables significant energy savings. The combination of robust housing, high-reflectance material and specially designed reflector add up to a high-efficiency luminaire that can help drive profitability by improving energy efficiency.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Light Technical	
Number of light sources	2
Optic type	Medium beam
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	54 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible

Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	TPS550 2XTL5-54W HFP MB
Full product name	TPS550 2XTL5-54W HFP MB
Full product code	910403630505
Order code	910403630505
Material Nr. (12NC)	910403630505
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## ProLux TPS550 C

### Dimensional drawing

