



# ProLux TPS550 C

## TPS550 2xTL5-54W HFR NB W3

2, TL5, 54 W, HF Regulator, Narrow beam, Plug-in connector 3-pole Wieland/Adels compatible

In industry, the bottom line is affected by a whole host of factors – worker productivity, running costs and maintenance, to name just a few. In today's economic environment, with margins under pressure, all businesses operating high-bay facilities are faced with the pressing need to save energy. Our ProLux high-bay solution is a direct replacement for current HID high-bay systems and enables significant energy savings. The combination of robust housing, high-reflectance material and specially designed reflector add up to a high-efficiency luminaire that can help drive profitability by improving energy efficiency.

### Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Gear	HFR [HF Regulator]		
Light Technical		Product Data	
Number of light sources	2	Order product name	TPS550 2xTL5-54W HFR NB W3
Optic type	Narrow beam	Full product name	TPS550 2xTL5-54W HFR NB W3
		Full product code	910403630538
		Order code	910403630538
		Material Nr. (12NC)	910403630538
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
Operating and Electrical			
Input Voltage	220 to 240 V		
Power Consumption	54 W		
Connection	Plug-in connector 3-pole Wieland/Adels compatible		

## ProLux TPS550 C

### Dimensional drawing

