



ProLux TPS550 C

TPS550 2xTL5-28W EBP NB W3

2, TL5, 28 W, Electronic Primalume, Narrow beam, Plug-in connector 3-pole Wieland/Adels compatible

In industry, the bottom line is affected by a whole host of factors – worker productivity, running costs and maintenance, to name just a few. In today's economic environment, with margins under pressure, all businesses operating high-bay facilities are faced with the pressing need to save energy. Our ProLux high-bay solution is a direct replacement for current HID high-bay systems and enables significant energy savings. The combination of robust housing, high-reflectance material and specially designed reflector add up to a high-efficiency luminaire that can help drive profitability by improving energy efficiency.

Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Gear	EBP [Electronic Primalume]		
Light Technical		Product Data	
Number of light sources	2	Order product name	TPS550 2xTL5-28W EBP NB W3
Optic type	Narrow beam	Full product name	TPS550 2xTL5-28W EBP NB W3
		Full product code	910403630556
		Order code	910403630556
		Material Nr. (12NC)	910403630556
Operating and Electrical		Numerator - Quantity Per Pack	1
Input Voltage	220 to 240 V	Numerator - Packs per outer box	1
Power Consumption	28 W		
Connection	Plug-in connector 3-pole Wieland/Adels compatible		

ProLux TPS550 C

Dimensional drawing

