



Intelligent Sereno TBS869/528

TBS869 C 2xTL5-28W HFR D8 LX FTB

2, TL5, 28 W, HF Regulator, Semi-high-gloss optic 3D micro-lamellae, Luxsense, Fused terminal block

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information		Approval and Application	
Lamp family code	TL5 [TL5]	Ingress protection code	IP20 [Finger-protected]
Gear	HFR [HF Regulator]	Product Data	
Embedded control	Luxsense	Order product name	TBS869 C 2xTL5-28W HFR D8 LX FTB
Light Technical		Full product name	TBS869 C 2xTL5-28W HFR D8 LX FTB
Number of light sources	2	Full product code	910403630607
Optic type	Semi-high-gloss optic 3D micro-lamellae	Order code	910403630607
Operating and Electrical		Material Nr. (12NC)	910403630607
Power Consumption	28 W	Numerator - Quantity Per Pack	1
Cable	-	Numerator - Packs per outer box	1

Intelligent Sereno TBS869/528

Dimensional drawing

