



Intelligent Sereno TBS869/528

TBS869 C 3xTL5-28W HFR D8 LX FTB

3, TL5, 28 W, HF Regulator, Semi-high-gloss optic 3D micro-lamellae, Luxsense, Fused terminal block

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information		Approval and Application	
Lamp family code	TL5 [TL5]	Ingress protection code	IP20 [Finger-protected]
Gear	HFR [HF Regulator]		
Embedded control	Luxsense	Product Data	
		Order product name	TBS869 C 3xTL5-28W HFR D8 LX FTB
		Full product name	TBS869 C 3xTL5-28W HFR D8 LX FTB
		Full product code	910403630609
		Order code	910403630609
		Material Nr. (12NC)	910403630609
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
Light Technical			
Number of light sources	3		
Optic type	Semi-high-gloss optic 3D micro-lamellae		
Operating and Electrical			
Power Consumption	28 W		
Cable	-		

Intelligent Sereno TBS869/528

Dimensional drawing

